

機 型 Model	JC-FSB	JC-FSC
生產速度 Speed (bpm)	30-60	
使用電源 Power Source (VAC)	220V/380V 50HZ/60H	Z single phase/3 phase
電機功率 Power Consumption (kw)	1.5	
耗 氣 量 Air Consumption (min)	4-6 Kgs x 70 Liter	
機器重量 Machine Weight (kg)	900	

紀正機械有限公司

Jih Cheng Machinery Technologies Co., LTD 新北市樹林區大安路502號7樓

7F. No.502 Da-An Rd. Shulin Dist., New Taipei City 23849, Taiwan : +886-2-26758968 : +886-2-26758229


: sales@jihcheng.com www.jihcheng.com

上海紀正機械有限公司

Shanghai Jih Cheng Machinery Mfg Co., LTD 上海市閔行區華漕鎭鳴嘉路318號

318, Mingjia Rd., Huacao Town, MinHang Section, ShangHai, China :+86-21-52265388 ::+86-21-52265658

: sales@jihcheng.com www.jihcheng.com



自動液體充填封蓋機 **Automatic Filling** & Overcapping Machine





蓋作業。

This machine is design for medium volume filling & overcapping operations.



自動液體充填封蓋機

本機為具有充填、封蓋能力的機型,專門使用在中等容量的液體包裝作業,尤其對於無菌室的空間硬體設備之能 源消耗,頗具節省與精簡之功效。使用PLC邏輯控制器及各種檢測感應裝置,將充填、封蓋一次完成,符合cGMP 之標準。適用於眼藥水、水型針劑、口服液、化妝品、香精等的自動包裝。

Automatic Filling & Overcapping Machine

This monoblock machine incorporates filling and over-cap sealing functions. It is mainly used in medium volume liquid packing applications. Being compact, minimal energy consumption, the machine is especially suitable for use inside a sterile area. With PLC and other photoelectric sensor controls, the filling & cap sealing operations are completed meeting cGMP requirement. It is suitable for eye drop, medium volume liquid injectable, oral solution, cosmetics, volatile oil packing applications.



充填

充填設計可採用充填幫浦定量設計或蠕動幫浦充填系統,充填量可以 進行個別調整或全部調整,並有電眼監視控制,達到『有瓶充填,無 瓶不充填』。

Filling

Filling system can choice piston pump or peristaltic pump, it is allows for volume adjustment separateor complete set of pump. There is a photo sensor for bottle detection to achieve of Bottle-Filling and No-Bottle-No Filling.



伺服控制

充填系統採用伺服控制,連接 PLC 和人機介面可直接在人機調整 充填量

Servo system

Filling system adopt servo motor control, connectiong with PLC, filing volume can be adjusted on HMI.

星解扭力過載

星盤附有扭力過載跳脫停機安全裝置

Starwheel over load

For safety, machine stops immediately when starwheel over



充填系統搭配封蓋或旋蓋功能, 達到一機多功能的效果

Filling system with cap sealing or plastic capping head to reach mulit-function model.



旋蓋位置上設計有瓶子固定裝置,且旋蓋 頭設計有扭力調整裝置,可依不同需求白 由調整瓶蓋緊實度;旋蓋頭可依瓶蓋尺寸 不同,輕易的進行更換。

Screw capping

There is a bottle clasping device at the sealing station, while the sealing head equipped with adjustable torgus as needed for individual cap & bottle in addition to tension absorbing mechanism to extend sealing durability. It is easy in bottle size change-over for different bottle cap size.



封蓋頭設計為四片滾刀,並可自由調整 封蓋緊實度,瓶蓋美觀不易受損,可依 瓶蓋尺寸不同,輕易的進行更換封蓋頭 , 滿足客戶不同需求。

Roll-on cap sealing

The sealing head is a sealing roller design, possible for adjustment of cap sealing tightness without affecting smooth appearance of caps. It is easy in bottle size change-over for different bottle cap sizes.